

Metl-Span III, urethane insulated panels
Weight in PSF

Thickness	Panel Type	Facing Gage (Face 1/Face2)								
		26/26	24/26	22/26	26/24	24/24	22/24	26/22	24/22	22/22
2"	CF-45	2.10	2.32	2.58	2.32	2.54	2.80	2.58	2.80	3.06
	CF-42	2.14	2.35	2.65	2.35	2.58	2.86	2.61	2.84	3.12
	CF-36	2.15	2.36	2.66	2.37	2.60	2.88	2.62	2.86	3.14
	CF-30	2.18	2.42	2.71	2.40	2.64	2.93	2.64	2.91	3.20
	CF-24	2.23	2.49	2.79	2.46	2.72	3.02	2.70	2.99	3.29
2.5"	CF-45	2.20	2.42	2.68	2.42	2.64	2.90	2.68	2.90	3.16
	CF-42	2.24	2.45	2.75	2.45	2.68	2.96	2.71	2.94	3.22
	CF-36	2.26	2.46	2.76	2.47	2.70	2.98	2.72	2.96	3.24
	CF-30	2.28	2.52	2.81	2.50	2.74	3.03	2.74	3.01	3.30
	CF-24	2.33	2.59	2.89	2.56	2.82	3.12	2.80	3.09	3.39
2.75"	CF-45	2.26	2.48	2.73	2.48	2.68	2.92	2.73	2.92	3.19
	CF-42	2.30	2.51	2.80	2.51	2.72	2.98	2.76	3.02	3.25
	CF-36	2.32	2.52	2.81	2.53	2.74	3.00	2.77	3.04	3.27
	CF-30	2.34	2.58	2.86	2.56	2.78	3.05	2.78	3.09	3.33
	CF-24	2.39	2.65	2.93	2.63	2.86	3.14	2.84	3.17	3.42
3"	CF-45	2.31	2.53	2.79	2.53	2.75	3.01	2.79	3.01	3.27
	CF-42	2.35	2.56	2.86	2.56	2.79	3.07	2.82	3.05	3.33
	CF-36	2.37	2.57	2.87	2.58	2.81	3.09	2.83	3.07	3.35
	CF-30	2.39	2.63	2.92	2.61	2.85	3.14	2.85	3.12	3.41
	CF-24	2.44	2.70	3.00	2.67	2.93	3.23	2.91	3.20	3.50
4"	CF-45	2.51	2.73	2.99	2.73	2.95	3.21	2.99	3.21	3.47
	CF-42	2.55	2.76	3.06	2.76	2.99	3.27	3.02	3.25	3.53
	CF-36	2.57	2.77	3.07	2.78	3.01	3.29	3.03	3.27	3.55
	CF-30	2.59	2.83	3.12	2.81	3.05	3.34	3.05	3.32	3.61
	CF-24	2.64	2.90	3.20	2.87	3.13	3.43	3.11	3.40	3.70
5"	CF-45	2.72	2.94	3.20	2.94	3.16	3.42	3.20	3.42	3.68
	CF-42	2.76	2.97	3.27	2.97	3.20	3.48	3.23	3.46	3.74
	CF-36	2.78	2.98	3.28	2.99	3.22	3.50	3.24	3.48	3.76
	CF-30	2.80	3.04	3.33	3.02	3.26	3.55	3.26	3.53	3.82
	CF-24	2.85	3.11	3.41	2.18	3.34	3.64	3.32	3.61	3.91
6"	CF-45	2.93	3.15	3.41	3.15	3.37	3.63	3.41	3.63	3.89
	CF-42	2.97	3.18	3.46	3.18	3.41	3.69	3.44	3.67	3.95
	CF-36	2.99	3.19	3.49	3.20	3.43	3.71	3.45	3.69	3.97
	CF-30	3.01	3.25	3.54	3.23	3.47	3.76	3.47	3.74	4.03
	CF-24	3.06	3.32	3.62	3.39	3.55	3.85	3.53	3.82	4.12

The above numbers are based on a core density of 2.50 pcf.

The weight of the different panel facings are as follows:

26 gage: .7752 psf

24 gage: .9792 psf

22 gage: 1.224 psf